

Axial expansion joint DN 90

Oper. pressure [bar]: 3

Oper. temp. range [K]: 20 ÷ 310

Oper. travel ranges (max.)

- axial [m] : -60 ÷ +64

Weight (max) [Kg] : 7.4

Spring rates (max.)

- axial [N/mm] : 30

Operating fluids : GHe, GN2

Bellows material : AISI 316 L

Application : A5 EPC press. lines

Status : Qualified for flight

