

SERIES 52

STANDARD RUBBER WHEELS AND POLYPROPYLENE CENTRE



Wheel description

Standard rubber tread; hardness 85 +/-3 Shore A. Polypropylene centre.

Hub

The hub is available with plain bearing and with roller bearing.

Diameters: 80-250 mm

Carrying capacity: 65-300 daN

Fittings with swivel, fixed and swivel with brake brackets



Standard duty brackets type NL - NLX

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems

Uses

Environments

Suitable for humid environments, with medium-harsh chemicals; not suitable for applications where organic solvents, chlorinated substances, hydrocarbons and mineral oils are present; it can be fitted under charts and trolleys of any kind, with light and standard carrying capacity. It can be used also for outdoor applications.

Typical usage: trolleys for indoor and outdoor industrial handling, bin containers.

Usage temperatures: from -20° C a +60°C

Floors



Handling

